

PROCEEDINGS OF SPIE

Advanced Lasers, High-Power Lasers, and Applications XIV

Jun Liu
Shibin Jiang
Ingmar Hartl
Editors

14–16 October 2023
Beijing, China

Sponsored by
SPIE
COS—Chinese Optical Society

Cooperating Organizations

Tsinghua University (China) • Peking University (China) • University of Science and Technology of China (China) • Zhejiang University (China) • Tianjin University (China) • Beijing Institute of Technology (China) • Beijing University of Posts and Telecommunications (China) • Nankai University (China) • Changchun University of Science and Technology (China) • University of Shanghai for Science and Technology (China) • Capital Normal University (China) • Huazhong University of Science and Technology (China) • Beijing Jiaotong University (China) • China Jiliang University (China) • Shanghai Institute of Optics and Fine Mechanics, CAS (China) • Changchun Institute of Optics, Fine Mechanics and Physics, CAS (China) • Institute of Semiconductors, CAS (China) • Institute of Optics and Electronics, CAS (China) • Institute of Physics, CAS (China) • Shanghai Institute of Technical Physics, CAS (China) • China Instrument and Control Society (China) • Optical Society of Japan (Japan) • Optical Society of Korea (Republic of Korea) • Australian and New Zealand Optical Society • Optics and Photonics Society of Singapore (Singapore) • European Optical Society

Supporting Organizations

China Association for Science and Technology (CAST) (China)
Department of Information of National Nature Science Foundation, China (NSFC) (China)

Published by
SPIE

Volume 12760

Proceedings of SPIE 0277-786X, V. 12760

SPIE is an international society advancing an interdisciplinary approach to the science and application of light.

The papers in this volume were part of the technical conference cited on the cover and title page. Papers were selected and subject to review by the editors and conference program committee. Some conference presentations may not be available for publication. Additional papers and presentation recordings may be available online in the SPIE Digital Library at SPIDigitalLibrary.org.

The papers reflect the work and thoughts of the authors and are published herein as submitted. The publisher is not responsible for the validity of the information or for any outcomes resulting from reliance thereon.

Please use the following format to cite material from these proceedings:

Author(s), "Title of Paper," in *Advanced Lasers, High-Power Lasers, and Applications XIV*, edited by Jun Liu, Shibin Jiang, Ingmar Hartl, Proc. of SPIE 12760, Seven-digit Article CID Number (DD/MM/YYYY); (DOI URL).

ISSN: 0277-786X

ISSN: 1996-756X (electronic)

ISBN: 9781510667693

ISBN: 9781510667709 (electronic)

Published by

SPIE

P.O. Box 10, Bellingham, Washington 98227-0010 USA

Telephone +1 360 676 3290 (Pacific Time)

SPIE.org

Copyright © 2023 Society of Photo-Optical Instrumentation Engineers (SPIE).

Copying of material in this book for internal or personal use, or for the internal or personal use of specific clients, beyond the fair use provisions granted by the U.S. Copyright Law is authorized by SPIE subject to payment of fees. To obtain permission to use and share articles in this volume, visit Copyright Clearance Center at copyright.com. Other copying for republication, resale, advertising or promotion, or any form of systematic or multiple reproduction of any material in this book is prohibited except with permission in writing from the publisher.

Printed in the United States of America by Curran Associates, Inc., under license from SPIE.

Publication of record for individual papers is online in the SPIE Digital Library.

**SPIE. DIGITAL
LIBRARY**

SPIDigitalLibrary.org

Paper Numbering: A unique citation identifier (CID) number is assigned to each article in the Proceedings of SPIE at the time of publication. Utilization of CIDs allows articles to be fully citable as soon as they are published online, and connects the same identifier to all online and print versions of the publication. SPIE uses a seven-digit CID article numbering system structured as follows:

- The first five digits correspond to the SPIE volume number.
- The last two digits indicate publication order within the volume using a Base 36 numbering system employing both numerals and letters. These two-number sets start with 00, 01, 02, 03, 04, 05, 06, 07, 08, 09, 0A, 0B ... 0Z, followed by 10-1Z, 20-2Z, etc. The CID Number appears on each page of the manuscript.

Contents

vii *Symposium Committee*
xi *Conference Committee*

SESSION 1 ULTRAFAST AND ADVANCED SOLID LASERS I

- 12760 03 **Sub-30 fs mode-locked Yb:(Y,Gd)AlO₃ laser** [12760-2]
- 12760 04 **Terbium aluminum garnet and terbium hafnium pyrochlore ceramics for high-power magneto-optical applications** [12760-3]
- 12760 05 **Polarization self-modulation of the coaxial diode-end-pumped orthogonally polarized laser induced by an intracavity waveplate** [12760-4]
- 12760 06 **High-energy gradient doped Yb:YAG thin slab laser amplifier** [12760-5]

SESSION 2 ULTRAFAST AND ADVANCED SOLID LASERS II

- 12760 08 **Simulation of the transient thermal effect for end-pumped Nd:YAG crystals operation at the repetition rate of 1 kHz** [12760-7]
- 12760 09 **Pulse-jitter reduction in passively Q-switched Nd:YAG/Cr:YAG microchip lasers by injection seeding actively Q-switched laser pulses** [12760-8]
- 12760 0A **Optimization of diode array side-pumped passively Q-switched Yb:Er:glass laser** [12760-9]

SESSION 3 LASER TECHNOLOGIES FOR LARGE FACILITIES I

- 12760 0B **High-power fiber laser system for the SHINE photo-injector (Invited Paper)** [12760-10]
- 12760 0C **Ultra-broadband and large aperture gratings for single-cycle Exawatt lasers** [12760-11]
- 12760 0D **Improved self-referenced spectral interferometry for large chirped pulses** [12760-12]

SESSION 4 LASER TECHNOLOGIES FOR LARGE FACILITIES II

- 12760 0G **Analysis of beam combining efficiency for filled-aperture** [12760-15]

SESSION 5 ADVANCED LASERS AND APPLICATIONS I

- 12760 0L **Optimization of random FBG array in multimode graded-index fiber for Raman lasing with improved spatio-spectral characteristics** [12760-20]
- 12760 0M **Uncertainty on Brillouin scattering measurements on bulk materials using a power laser** [12760-23]

SESSION 6 ADVANCED LASERS AND APPLICATIONS II

- 12760 0N **High-precision timing detection technology based on low-power ultrafast lasers (Invited Paper)** [12760-21]
- 12760 0O **An alignment-free laser based on cat-eye retroreflectors** [12760-47]

SESSION 7 INNOVATIVE LASERS I

- 12760 0S **Research on solid-core ARF coupler for fiber laser amplification** [12760-48]

SESSION 8 INNOVATIVE LASERS II

- 12760 0U **7.2W 3.5 μ m Er-doped ZBLAN fiber laser with optimized pump wavelength** [12760-28]
- 12760 0V **Towards intelligent fiber laser design by using a feed-forward neural network** [12760-29]
- 12760 0W **All-fiber mode-locked-laser at 920-nm wavelength** [12760-30]

SESSION 9 INNOVATIVE LASERS III

- 12760 0X **The generation of single-cavity triple-comb pulses from a wavelength/polarization multiplexed fiber laser** [12760-31]

POSTER SESSION

- 12760 10 **Mode-locked fiber laser based on ZrTe₂ saturable absorber** [12760-33]
- 12760 11 **High-power fiber-coupled diode laser module with mini-bar stack** [12760-35]

- 12760 13 **19×1 signal combiner for 10kW-level high-power fiber laser** [12760-37]
- 12760 14 **The temporal characteristics of Ne-like Ar 46.9nm x-ray laser pulse** [12760-38]
- 12760 15 **Fabrication of chirped and tilted fiber Bragg gratings for single-mode fiber lasers** [12760-39]
- 12760 16 **Dark-bright pair between bright pulses in a multimodal interference-based Q-switched mode-locking fiber laser** [12760-40]
- 12760 17 **15-mJ and high-peak-power nanosecond pulse based on all-fiber MOPA system** [12760-41]
- 12760 18 **A 3kW single-mode continuous laser based on multi-stage amplifiers fiber system** [12760-42]
- 12760 1B **Estimation method on energy utilization rate of laser eavesdropping system influenced by ambient temperature fluctuation** [12760-45]
- 12760 1C **Dual-comb spectroscopy for on-site spectroscopic detection** [12760-49]

DIGITAL POSTER SESSION

- 12760 1D **EDFA-enabled resonance beam charging at 1550 nm for improved efficiency, safety, and performance** [12760-22]